
## SHIELDED COIL FORMS

Fax (714) 970-0800



L41-2-BT-F-5 RED CARBONYL E .25-10 MHZ 10.0 115 95 ppm/°C 11.5 64 L41-3-BT-F-5 **GREY** CARBONYL HP .02-1.0 MHZ 35.0 15 150 66 370 ppm/°C L41-6-BT-F-5 YELLOW CARBONYL SF 2.0-50 MHZ 105 8.5 10.5 63 35 ppm/°C L41-10-BT-F-5 **BLACK** CARBONYL W 10-100 MHZ 6.0 8 80 62 150 ppm/°C L41-17-BT-F-5 LAVENDER CARBONYL 20-200 MHZ 4 6 60 50 50 ppm/°C

- 1) The iron powder or ferrite materials are used in the tuning core and cup core.
- 2) This represents the frequency range for Q optimization in tuned or resonant circuits. The inductive properties of the material is effective over a considerably wider frequency range.
- 3) Nanohenries (10<sup>-9</sup> Henries) per turn squared.
- 4) The minimum inductance is measured in microhenries (10<sup>-6</sup> Henries) per 100 turns with the tuning core tuned
- out of the winding area but still a part of the assembly.
- 5) The temperature stability is of the magnetic material, measured in parts per million per degree Celsius (ppm/°C) on a toroidal core and winding. This is only an indication of the temperature stability for a complete wound assembly.

